


KMA Series

- 7mm height
- Endurance : 1,000 hours at 105°C
- Solvent resistant type (see PRECAUTIONS AND GUIDELINES)
- RoHS Compliant




◆ SPECIFICATIONS


Items	Characteristics										
Category	-55 to +105°C										
Temperature Range	-55 to +105°C										
Rated Voltage Range	4 to 63V _{dc}										
Capacitance Tolerance	±20% (M) (at 20°C, 120Hz)										
Leakage Current	I=0.01CV or 3μA, whichever is greater. Where, I : Max. leakage current (μA), C : Nominal capacitance (μF), V : Rated voltage (V) (at 20°C after 2 minutes)										
Dissipation Factor (tan δ)	Rated voltage (V _{dc})	4V	6.3V	10V	16V	25V	35V	50V	63V		
	tan δ (Max.)	0.35	0.22	0.19	0.16	0.14	0.12	0.10	0.08	(at 20°C, 120Hz)	
Low Temperature Characteristics (Max. Impedance Ratio)	Rated voltage (V _{dc})	4V	6.3V	10V	16V	25V	35V	50V	63V		
	Z(-25°C)/Z(+20°C)	4	3	2	2	2	2	2	2	(at 120Hz)	
	Z(-40°C)/Z(+20°C)	10	6	5	3	3	3	3	3		
Endurance	The following specifications shall be satisfied when the capacitors are restored to 20°C after the rated voltage is applied for 1,000 hours at 105°C.										
	Rated voltage	4 to 16V _{dc}				25 to 63V _{dc}					
	Capacitance change	≤ ±25% of the initial value				≤ ±20% of the initial value					
	D.F. (tan δ)	≤ 200% of the initial specified value									
	Leakage current	≤ The initial specified value									
Shelf Life	The following specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1,000 hours at 105°C without voltage applied. Before the measurement, the capacitor shall be preconditioned by applying voltage according to Item 4.1 of JIS C 5101-4.										
	Rated voltage	4 to 16V _{dc}				25 to 63V _{dc}					
	Capacitance change	≤ ±25% of the initial value				≤ ±20% of the initial value					
	D.F. (tan δ)	≤ 200% of the initial specified value									
	Leakage current	≤ The initial specified value									

◆ DIMENSIONS [mm]

- Terminal Code : E
Sleeve (PET : Brown)




φD	4	5	6.3
φd	0.45	0.45	0.45
F	1.5	2.0	2.5
φD'	φD+0.5max.		
L'	L+1.0max.		



Gas escape end seal

◆ PART NUMBERING SYSTEM



Please refer to "Product code guide (radial lead type)"

◆ STANDARD RATINGS

WV (V _{dc})	Cap (μF)	Case size φD×L(mm)	tan δ	Rated ripple current (mA _{RMS} /105°C, 120Hz)	Part No.	WV (V _{dc})	Cap (μF)	Case size φD×L(mm)	tan δ	Rated ripple current (mA _{RMS} /105°C, 120Hz)	Part No.
4	33	4 × 7	0.35	26	EKMA4R0E□□330MD07D	35	4.7	4 × 7	0.12	20	EKMA350E□□4R7MD07D
	47	4 × 7	0.35	34	EKMA4R0E□□470MD07D		10	5 × 7	0.12	30	EKMA350E□□100ME07D
	100	5 × 7	0.35	61	EKMA4R0E□□101ME07D		22	6.3 × 7	0.12	47	EKMA350E□□220MF07D
	220	6.3 × 7	0.35	95	EKMA4R0E□□221MF07D		33	6.3 × 7	0.12	64	EKMA350E□□330MF07D
6.3	22	4 × 7	0.22	31	EKMA6R3E□□220MD07D	50	1.0	4 × 7	0.10	10	EKMA500E□□1R0MD07D
	47	5 × 7	0.22	47	EKMA6R3E□□470ME07D		2.2	4 × 7	0.10	15	EKMA500E□□2R2MD07D
10	33	5 × 7	0.19	43	EKMA100E□□330ME07D		3.3	4 × 7	0.10	18	EKMA500E□□3R3MD07D
	100	6.3 × 7	0.19	80	EKMA100E□□101MF07D		4.7	5 × 7	0.10	23	EKMA500E□□4R7ME07D
16	10	4 × 7	0.16	25	EKMA160E□□100MD07D		10	6.3 × 7	0.10	34	EKMA500E□□100MF07D
	22	5 × 7	0.16	39	EKMA160E□□220ME07D		22	6.3 × 7	0.10	57	EKMA500E□□220MF07D
	47	6.3 × 7	0.16	59	EKMA160E□□470MF07D	63	1.0	4 × 7	0.08	11	EKMA630E□□1R0MD07D
100	6.3 × 7	0.16	97	EKMA160E□□101MF07D	2.2		4 × 7	0.08	17	EKMA630E□□2R2MD07D	
25	33	6.3 × 7	0.14	53	EKMA250E□□330MF07D		3.3	5 × 7	0.08	21	EKMA630E□□3R3ME07D
	47	6.3 × 7	0.14	71	EKMA250E□□470MF07D		4.7	6.3 × 7	0.08	26	EKMA630E□□4R7MF07D
						10	6.3 × 7	0.08	43	EKMA630E□□100MF07D	

□□ : Enter the appropriate lead forming or taping code.