


NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. TERMINAL NUMBERS FOR REF. ONLY
3. TOLERANCE: X.X=± 0.4
X.XX=± 0.250
- ▲ 4. TRAVEL: LEVER 8°±2°; PUSH: 1.0mm +/- 0.2
5. RATING: 20mA @ 15 VDC
6. OPERATION FORCE: LEVER=280 +/- 100 gf
PUSH=500 +/- 150 gf
7. CONTACT RESISTANCE: 100 Milli-OHMS MAX.
8. LIFE CYCLES 100,000 CYCLES MIN.
7. ▲ DENOTES CRITICAL PARAMETER
8. 2002/95/EC (ROHS) COMPLIANT

C	19723	CHANGED DIMS was 12.02 & 6.59	2/28/11	BGL
B	19120	1mm R ADDED TO ACTUATOR STEM	6/4/10	BLR
A	10243	Release For Production	6/16/99	MM
REV	PCR NO	DESCRIPTION	DATE	BY



TITLE JS5208

SCALE 2.5 : 1	DATE 6/4/2010	DR BLR	DWG P200020	REV C
---------------	---------------	--------	-------------	-------