


Precision Thin Film Chip Resistors



Thin Film Flat Chip Resistors combine the proven reliability of the professional products with an advanced level of precision and stability. Therefore they are perfectly suited for applications in the fields of test and measuring equipment together with industrial and medical electronics.

FEATURES

- Approved according to EN 140401-801
- Low TCR: ± 10 ppm/K to ± 25 ppm/K
- Precision tolerance of value: $\pm 0.1\%$ and $\pm 0.25\%$
- Superior overall stability: Class 0.1 and 0.25
- Lead (Pb)-free solder contacts
- Compliant to RoHS directive 2002/95/EC



APPLICATIONS

- Automotive
- Test and measuring equipment
- Medical equipment
- Industrial equipment

METRIC SIZE

INCH:	0402	0603	0805	1206
METRIC:	RR 1005M	RR 1608M	RR 2012M	RR 3216M

TECHNICAL SPECIFICATIONS

DESCRIPTION	MCS 0402		MCT 0603		MCU 0805		MCA 1206			
Metric size	RR 1005M		RR 1608M		RR 2012M		RR 3216M			
Resistance range	100 Ω to 221 k Ω		39 Ω to 511 k Ω		39 Ω to 1.5 M Ω		39 Ω to 2 M Ω			
Resistance tolerance	$\pm 0.25\%$; $\pm 0.1\%$									
Temperature coefficient	± 25 ppm/K; ± 15 ppm/K; ± 10 ppm/K									
Operation mode	Precision	Standard	Precision	Standard	Precision	Standard	Precision	Standard		
Climatic category (LCT/UCT/days)	10/85/56	55/125/56	10/85/56	55/125/56	10/85/56	55/125/56	10/85/56	55/125/56		
Rated dissipation, P_{70} ⁽¹⁾	0.016 W	0.063 W	0.032 W	0.1 W	0.050 W	0.125 W	0.1 W	0.25 W		
Operating voltage, U_{max} AC/DC	12.5 V	50 V	25 V	75 V	35 V	150 V	50 V	200 V		
Film temperature	85 $^{\circ}$ C	125 $^{\circ}$ C	85 $^{\circ}$ C	125 $^{\circ}$ C	85 $^{\circ}$ C	125 $^{\circ}$ C	85 $^{\circ}$ C	125 $^{\circ}$ C		
Max. resistance change at P_{70} for resistance range, $ \Delta R/R $ max., after:	100 Ω to 221 k Ω		39 Ω to 511 k Ω		39 Ω to 1.5 M Ω		39 Ω to 2 M Ω			
	1000 h	$\leq 0.1\%$	$\leq 0.2\%$	$\leq 0.1\%$	$\leq 0.2\%$	$\leq 0.1\%$	$\leq 0.2\%$	$\leq 0.05\%$	$\leq 0.1\%$	
	8000 h	$\leq 0.2\%$	$\leq 0.4\%$	$\leq 0.2\%$	$\leq 0.4\%$	$\leq 0.2\%$	$\leq 0.4\%$	$\leq 0.1\%$	$\leq 0.25\%$	
	225 000 h	$\leq 0.5\%$	$\leq 1.0\%$	$\leq 0.5\%$	$\leq 1.0\%$	$\leq 0.5\%$	$\leq 1.0\%$	$\leq 0.25\%$	$\leq 0.5\%$	
Specified lifetime	225 000 h		225 000 h		225 000 h		225 000 h			
Insulation voltage:	1 min; U_{ins}		75 V		100 V		200 V		300 V	
	Continuous		75 V		75 V		75 V		75 V	
Failure rate: FIT _{observed}	$\leq 0.1 \times 10^{-9}/h$		$\leq 0.1 \times 10^{-9}/h$		$\leq 0.1 \times 10^{-9}/h$		$\leq 0.1 \times 10^{-9}/h$			

Note

⁽¹⁾ The power dissipation on the resistor generates a temperature rise against the local ambient, depending on the heat flow support of the printed-circuit board (thermal resistance). The rated dissipation applies only if the permitted film temperature is not exceeded.



MCS 0402, MCT 0603, MCU 0805, MCA 1206 - Precision

Precision Thin Film Chip Resistors

Vishay Beyschlag

PART NUMBER AND PRODUCT DESCRIPTION (1)																	
PART NUMBER: MCT06030D4641BPW00																	
M	C	T	0	6	0	3	0	D	4	6	4	1	B	P	W	0	0
MODEL/SIZE	SPECIAL CHARACTER		TCR		VALUE		TOLERANCE		PACKAGING		SPECIAL						
MCS0402 MCT0603 MCU0805 MCA1206	0 = Neutral		F = ± 10 ppm/K E = ± 15 ppm/K D = ± 25 ppm/K		3 digit value 1 digit multiplier MULTIPLIER 7 = *10 ⁻³ 2 = *10 ² 8 = *10 ⁻² 3 = *10 ³ 9 = *10 ⁻¹ 4 = *10 ⁴ 0 = *10 ⁰ 5 = *10 ⁵ 1 = *10 ¹ 6 = *10 ⁶		B = ± 0.1 % C = ± 0.25 %		P1 P5 PW E1 E0		Up to 2 digits 00 = Standard						
PRODUCT DESCRIPTION: MCT 0603 - 25 0.1 % PW 4K64																	
MCT	0603	- 25	0.1 %	PW	4K64												
MODEL	SIZE	TCR	TOLERANCE	PACKAGING	RESISTANCE VALUE												
MCS MCT MCU MCA	0402 0603 0805 1206	± 10 ppm/K ± 15 ppm/K ± 25 ppm/K	± 0.1 % ± 0.25 %	P1 P5 PW E1 E0	47K = 47 kΩ 50R1 = 50.1 Ω												

Note

(1) Products can be ordered using either the PRODUCT DESCRIPTION or the PART NUMBER

TEMPERATURE COEFFICIENT AND RESISTANCE RANGE					
DESCRIPTION		RESISTANCE VALUE (2)			
TCR	TOLERANCE	MCS 0402	MCT 0603	MCU 0805	MCA 1206
± 25 ppm/K	± 0.25 %	100 Ω to 221 kΩ	39 Ω to 511 kΩ	39 Ω to 1.5 MΩ	39 Ω to 2 MΩ
	± 0.1 %	150 Ω to 221 kΩ	47 Ω to 511 kΩ	47 Ω to 1.5 MΩ	47 Ω to 2 MΩ
± 15 ppm/K	± 0.25 %	100 Ω to 150 kΩ	39 Ω to 332 kΩ	39 Ω to 1 MΩ	39 Ω to 1.5 MΩ
	± 0.1 %	150 Ω to 150 kΩ	47 Ω to 332 kΩ	47 Ω to 1 MΩ	47 Ω to 1.5 MΩ
± 10 ppm/K (3)	± 0.25 %	100 Ω to 130 kΩ	39 Ω to 221 kΩ	39 Ω to 511 kΩ	39 Ω to 1 MΩ
	± 0.1 %	150 Ω to 130 kΩ	47 Ω to 221 kΩ	47 Ω to 511 kΩ	47 Ω to 1 MΩ

Notes


(2) Resistance values to be selected from E96 and E192 series, other values are available on request

(3) TCR 10 is specified over the temperature range from - 10 °C to 85 °C

Resistance ranges printed in bold are preferred TCR/tolerance combinations with optimized availability.


PACKAGING		
MODEL	REEL	
	PIECES/ PAPER TAPE ON REEL	CODE
MCS 0402	1000	E1
	10 000	E0
MCT 0603	1000	P1
	5000	P5
	20 000	PW
MCU 0805	1000	P1
	5000	P5
	20 000	PW
MCA 1206	1000	P1
	5000	P5

DIMENSIONS



DIMENSIONS AND MASS							
TYPE	H (mm)	L (mm)	W (mm)	W _T (mm)	T ₁ (mm)	T ₂ (mm)	MASS (mg)
MCS 0402	0.32 ± 0.05	1.0 ± 0.05	0.5 ± 0.05	> 75 % of W	0.2 + 0.1/- 0.15	0.2 ± 0.1	0.6
MCT 0603	0.45 + 0.1/- 0.05	1.55 ± 0.05	0.85 ± 0.1	> 75 % of W	0.3 + 0.15/- 0.2	0.3 + 0.15/- 0.2	1.9
MCU 0805	0.45 + 0.1/- 0.05	2.0 ± 0.1	1.25 ± 0.15	> 75 % of W	0.4 + 0.1/- 0.2	0.4 + 0.1/- 0.2	4.6
MCA 1206	0.55 ± 0.1	3.2 + 0.1/- 0.2	1.6 ± 0.15	> 75 % of W	0.5 ± 0.25	0.5 ± 0.25	9.2

SOLDER PAD DIMENSIONS



RECOMMENDED SOLDER PAD DIMENSIONS								
TYPE	WAVE SOLDERING				REFLOW SOLDERING			
	G (mm)	Y (mm)	X (mm)	Z (mm)	G (mm)	Y (mm)	X (mm)	Z (mm)
MCS 0402	-	-	-	-	0.35	0.55	0.55	1.45
MCT 0603	0.55	1.10	1.10	2.75	0.65	0.70	0.95	2.05
MCU 0805	0.80	1.25	1.50	3.30	0.90	0.90	1.40	2.70
MCA 1206	1.40	1.50	1.90	4.40	1.50	1.15	1.75	3.80

Note

- The given solder pad dimensions reflect the considerations for board design and assembly as outlined e.g. in standards IEC 61188-5-x, or in publication IPC-7351. They do not guarantee any supposed thermal properties, particularly as these are also strongly influenced by many other parameters.

Still, the given solder pad dimensions will be found adequate for most general applications, e.g. those referring to “standard operation mode”.



DESCRIPTION

Production is strictly controlled and follows an extensive set of instructions established for reproducibility. A homogeneous film of metal alloy is deposited on a high grade Al₂O₃ ceramic substrate and conditioned to achieve the desired temperature coefficient. Specially designed inner contacts are deposited on both sides. A special laser is used to achieve the target value by smoothly fine trimming the resistive layer without damaging the ceramics. A further conditioning is applied in order to stabilize the trimming result. The resistor elements are covered by a blue protective coating designed for electrical, mechanical and climatic protection. The terminations receive a final pure tin on nickel plating.

The result of the determined production is verified by an extensive testing procedure and optical inspection performed on 100 % of the individual chip resistors. Only accepted products are laid directly into the paper tape in accordance with **IEC 60286-3** ⁽³⁾.

ASSEMBLY

The resistors are suitable for processing on automatic SMD assembly systems and for automatic soldering using wave, reflow or vapour phase. The encapsulation is resistant to all cleaning solvents commonly used in the electronics industry, including alcohols, esters and aqueous solutions. The suitability of conformal coatings, if applied, shall be qualified by appropriate means to ensure the long-term stability of the whole system.

The resistors are RoHS compliant, the pure tin plating provides compatibility with lead (Pb)-free and lead-containing soldering processes. Solderability is specified for 2 years after production or requalification. The permitted storage time is 20 years. The immunity of the plating against tin whisker growth has been proven under extensive testing.

All products comply with the **GADSL** ⁽¹⁾ and the **CEFIC-EECA-EICTA** ⁽²⁾ list of legal restrictions on hazardous substances. This includes full compliance with the following directives:

- 2000/53/EC End of Vehicle life Directive (ELV) an Annex II (ELV II)
- 2002/95/EC Restriction of the use of Hazardous Substances Directive (RoHS)
- 2002/96/EC Waste Electrical and Electronic Equipment Directive (WEEE)

Notes


⁽¹⁾ Global Automotive Declarable Substance List, see www.gadsl.org

⁽²⁾ CEFIC (European Chemical Industry Council), EECA (European Electronic Component Manufacturers Association), EICTA (European trade organisation representing the information and communications technology and consumer electronics), see www.eicta.org/index.php?id=995
→ issues → environment policy → chemicals → chemicals for electronics

⁽³⁾ The quoted IEC standards are also released as EN standards with the same number and identical contents

APPROVALS

The resistors are approved within the IECQ-CECC Quality Assessment System for Electronic Components to the detail specification **EN 140401-801** which refers to **EN 60115-1**, **EN 140400** and the variety of environmental test procedures of the **IEC 60068** ⁽³⁾ series.

Conformity is attested by the use of the **CECC Logo** () as the Mark of Conformity on the package label.

Vishay BEYSCHLAG has achieved “**Approval of Manufacturer**” in accordance with **IEC QC 001002-3, clause 2**. The release certificate for “**Technology Approval Schedule**” in accordance with **CECC 240001** based on **IEC QC 001002-3, clause 6** is granted for the Vishay BEYSCHLAG manufacturing process.

RELATED PRODUCTS


On request, resistors are available with **established reliability** in accordance with **EN 140401-801** version E. Please refer to the special datasheet document no. **28744** for information on failure rate level, available resistance ranges and order codes.

For more information about products with higher rated power and higher operation temperature please refer to the **Professional Thin Film Chip Resistor** datasheet document no. **28705**.


Precision **chip resistor arrays** may be used in voltage divider applications or precision amplifiers where close matching between multiple resistors is necessary. Please refer to the ACAS 0612 - Precision datasheet document no. **28751**.




FUNCTIONAL PERFORMANCE



Derating - Standard Operation



Derating - Precision Operation



Current Noise A₁

In accordance with IEC 60195



TEST AND REQUIREMENTS

All tests are carried out in accordance with the following specifications:

EN 60115-1, generic specification (includes tests)

EN 140400, sectional specification (includes schedule for qualification approval)

EN 140401-801, detail specification (includes schedule for conformance inspection)

The components are approved in accordance with the European CECC-system, where applicable. The following table contains only the most important tests. For the full test schedule refer to the documents listed above. The testing also covers most of the requirements specified by EIA/IS-703 and JIS-C-5202.

The tests are carried out in accordance with IEC 60068 and under standard atmospheric conditions in accordance with

IEC 60068-1, 5.3. Climatic category LCT/UCT/56 (rated temperature range: Lower Category Temperature, Upper Category Temperature; damp heat, long term, 56 days) is valid. Unless otherwise specified the following values apply:

Temperature: 15 °C to 35 °C

Relative humidity: 45 % to 75 %

Air pressure: 86 kPa to 106 kPa (860 mbar to 1060 mbar).

The components are mounted for testing on boards in accordance with EN 60115-1, 4.31 unless otherwise specified.

The parameters stated in the Test Procedures and Requirements table are based on the required tests and permitted limits of EN 140401-801. However, some additional tests and a number of improvements against those minimum requirements have been included.

TEST PROCEDURES AND REQUIREMENTS					
EN 60115-1 CLAUSE	IEC 60068-2 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (ΔR)	
				STABILITY CLASS 0.1	STABILITY CLASS 0.25
			Stability for product types:		
			MCS 0402	470 Ω to 10 k Ω	> 10 k Ω to 52.3 k Ω
			MCT 0603	100 Ω to 10 k Ω	39 Ω to < 100 Ω ; > 10 k Ω to 511 k Ω
			MCU 0805	100 Ω to 47.5 k Ω	39 Ω to < 100 Ω ; > 47.5 k Ω to 1.5 M Ω
			MCA 1206	47 Ω to 332 k Ω	39 Ω to < 47 Ω ; > 332 k Ω to 2 M Ω
4.5	-	Resistance		$\pm 0.1 \% R$; $\pm 0.25 \% R$	
4.8.4.2	-	Temperature coefficient	At (20/- 10/20) °C and (20/85/20) °C	± 25 ppm/K; ± 15 ppm/K; ± 10 ppm/K	
4.25.1	-	Endurance at 70 °C: Precision operation mode	$U = \sqrt{P_{70}} \times \bar{R}$ or $U = U_{max.}$; whichever is the less severe; 1.5 h on; 0.5 h off; 70 °C; 1000 h 70 °C; 8000 h	$\pm (0.1 \% R + 0.02 \Omega)^{(1)}$ $\pm (0.2 \% R + 0.02 \Omega)^{(1)}$	
		Endurance at 70 °C: Standard operation mode	$U = \sqrt{P_{70}} \times \bar{R}$ or $U = U_{max.}$; whichever is the less severe; 1.5 h on; 0.5 h off; 70 °C; 1000 h 70 °C; 8000 h	$\pm (0.2 \% R + 0.02 \Omega)^{(1)}$ $\pm (0.4 \% R + 0.05 \Omega)^{(1)}$	
4.25.3	-	Endurance at upper category temperature	85 °C; 1000 h 125 °C; 1000 h	$\pm (0.1 \% R + 0.02 \Omega)$ $\pm (0.2 \% R + 0.02 \Omega)$	$\pm (0.2 \% R + 0.02 \Omega)$ $\pm (0.25 \% R + 0.05 \Omega)$
4.24	78 (Cab)	Damp heat, steady state	(40 \pm 2) °C; 56 days; (93 \pm 3) % RH	$\pm (0.1 \% R + 0.02 \Omega)$	$\pm (0.25 \% R + 0.05 \Omega)$



TEST PROCEDURES AND REQUIREMENTS					
EN 60115-1 CLAUSE	IEC 60068-2 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (ΔR)	
				STABILITY CLASS 0.1	STABILITY CLASS 0.25
			Stability for product types:		
			MCS 0402	470 Ω to 10 k Ω	> 10 k Ω to 52.3 k Ω
			MCT 0603	100 Ω to 10 k Ω	39 Ω to < 100 Ω ; > 10 k Ω to 511 k Ω
			MCU 0805	100 Ω to 47.5 k Ω	39 Ω to < 100 Ω ; > 47.5 k Ω to 1.5 M Ω
			MCA 1206	47 Ω to 332 k Ω	39 Ω to < 47 Ω ; > 332 k Ω to 2 M Ω
4.23 4.23.2 4.23.3 4.23.4 4.23.5 4.23.6	2 (Ba) 30 (Db) 1 (Aa) 13 (M) 30 (Db)	Climatic sequence: dry heat damp heat, cyclic cold low air pressure damp heat, cyclic	UCT; 16 h 55 °C; 24 h; > 90 % RH; 1 cycle LCT; 2 h 8.5 kPa; 2 h; (25 \pm 10) °C 55 °C; 5 days; > 95 % to 100 % RH; 5 cycles LCT = - 55 °C; UCT = 125 °C	$\pm (0.1 \% R + 0.02 \Omega)$	$\pm (0.25 \% R + 0.05 \Omega)$
-	1 (Aa)	Cold	- 55 °C; 2 h	$\pm (0.05 \% R + 0.01 \Omega)$	
4.19	14 (Na)	Rapid change of temperature	30 min at LCT and 30 min at UCT; LCT = - 10 °C UCT = 85 °C; 5 cycles	$\pm (0.05 \% R + 0.01 \Omega)$ no visible damage	
			LCT = - 55 °C; UCT = 125 °C; 1000 cycles	$\pm (0.25 \% R + 0.05 \Omega)$ no visible damage	
4.13	-	Short time overload; precision operation mode	$U = 2.5 \times \sqrt{P_{70} \times R}$ or $U = 2 \times U_{max.}$; whichever is the less severe; 5 s	$\pm (0.05 \% R + 0.01 \Omega)$	
		Short time overload; standard operation mode		$\pm (0.05 \% R + 0.01 \Omega)$	
4.27	-	Single pulse high voltage overload; standard operation mode	Severity no. 4: $U = 10 \times \sqrt{P_{70} \times R}$ or $U = 2 \times U_{max.}$; whichever is the less severe; 10 pulses 10 μ s/700 μ s	$\pm (0.5 \% R + 0.05 \Omega)^{(2)}$ no visible damage	
4.37	-	Periodic electric overload; standard operation mode	$U = \sqrt{15 \times P_{70} \times R}$ or $U = 2 \times U_{max.}$; whichever is the less severe; 0.1 s on; 2.5 s off; 1000 cycles	$\pm (0.5 \% R + 0.05 \Omega)^{(2)}$ no visible damage	
4.22	6 (Fc)	Vibration	Endurance by sweeping; 10 Hz to 2000 Hz; no resonance; amplitude \leq 1.5 mm or \leq 200 m/s ² ; 6 h	$\pm (0.05 \% R + 0.01 \Omega)$ no visible damage	



TEST PROCEDURES AND REQUIREMENTS					
EN 60115-1 CLAUSE	IEC 60068-2 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (ΔR)	
				STABILITY CLASS 0.1	STABILITY CLASS 0.25
			Stability for product types:		
			MCS 0402	470 Ω to 10 k Ω	> 10 k Ω to 52.3 k Ω
			MCT 0603	100 Ω to 10 k Ω	39 Ω to < 100 Ω ; > 10 k Ω to 511 k Ω
			MCU 0805	100 Ω to 47.5 k Ω	39 Ω to < 100 Ω ; > 47.5 k Ω to 1.5 M Ω
			MCA 1206	47 Ω to 332 k Ω	39 Ω to < 47 Ω ; > 332 k Ω to 2 M Ω
4.17.2	58 (Td)	Solderability	Solder bath method; SnPb40; non-activated flux (215 \pm 3) $^{\circ}$ C; (3 \pm 0.3) s Solder bath method; SnAg3Cu0.5 or SnAg3.5; non-activated flux (235 \pm 3) $^{\circ}$ C; (2 \pm 0.2) s	Good tinning (\geq 95 % covered); no visible damage	
4.18.2	58 (Td)	Resistance to soldering heat	Solder bath method; (260 \pm 5) $^{\circ}$ C; (10 \pm 1) s	\pm (0.05 % R + 0.01 Ω)	
4.29	45 (XA)	Component solvent resistance	Isopropyl alcohol + 50 $^{\circ}$ C; method 2	No visible damage	
4.32	21 (Ue ₃)	Shear (adhesion)	RR 1005M and RR 1608M; 9 N RR 2012M and RR 3216M; 45 N	No visible damage	
4.33	21 (Ue ₁)	Substrate bending	Depth 2 mm, 3 times	\pm (0.05 % R + 0.01 Ω) no visible damage, no open circuit in bent position	
4.7	-	Voltage proof	$U_{RMS} = U_{ins}$; (60 \pm 5) s	No flashover or breakdown	
4.35	-	Flammability	IEC 60695-2-2, needle flame test; 10 s	No burning after 30 s	
Special requirements for type MCA 1206					
4.25.1	-	Endurance at 70 $^{\circ}$ C: Precision operation mode	$U = \sqrt{P_{70} \times R}$ or $U = U_{max}$; whichever is the less severe; 70 $^{\circ}$ C; 1000 h 70 $^{\circ}$ C; 8000 h	\pm (0.05 % R + 0.02 Ω) \pm (0.1 % R + 0.02 Ω)	
	-	Endurance at 70 $^{\circ}$ C: Standard operation mode	$U = \sqrt{P_{70} \times R}$ or $U = U_{max}$; whichever is the less severe; 70 $^{\circ}$ C; 1000 h 70 $^{\circ}$ C; 8000 h	\pm (0.1 % R + 0.02 Ω) \pm (0.25 % R + 0.05 Ω)	

Notes

(1) See 4.25.1 (above): special requirements for type MCA 1206

(2) The pulse load stability of professional MFC resistors applies for precision resistors also. However, severe pulse loads are likely to jeopardise precision stability requirements.

12NC INFORMATION FOR HISTORICAL CODING REFERENCE ONLY

- The resistors have a 12-digit numeric code starting with 2312.
- The subsequent 4 digits indicate the resistor type, specification and packaging; see the 12NC table.
- The remaining 4 digits indicate the resistance value:
 - The first 3 digits indicate the resistance value.
 - The last digit indicates the resistance decade in accordance with the 12NC Indicating Resistance Decade table.

Last Digit of 12NC Indicating Resistance Decade

RESISTANCE DECADE	LAST DIGIT
10 Ω to 99.9 Ω	9
100 Ω to 999 Ω	1
1 kΩ to 9.99 kΩ	2
10 kΩ to 99.9 kΩ	3
100 kΩ to 999 kΩ	4
1 MΩ to 9.99 MΩ	5

12NC Example

The 12NC of a MCT 0603 resistor, value 47 kΩ and TCR 25 with ± 0.1 % tolerance, supplied in cardboard tape of 5000 units per reel is: 2312 216 74703.

12NC - Resistors type and packaging							
DESCRIPTION			CODE 2312... ..				
			CARDBOARD TAPE ON REEL				
TYPE	TCR	TOL.	P1 1000 UNITS	P5 5000 UNITS	PW 20 000 UNITS	E1 1000 UNITS	E0 10 000 UNITS
MCS 0402	± 25 ppm/K	± 0.25 %	-	-	-	261 6...	276 6...
		± 0.1 %	-	-	-	261 7...	276 7...
	± 15 ppm/K	± 0.25 %	-	-	-	262 6...	277 6...
		± 0.1 %	-	-	-	262 7...	277 7...
	± 10 ppm/K	± 0.25 %	-	-	-	263 6...	278 6...
		± 0.1 %	-	-	-	263 7...	278 7...
MCT 0603	± 25 ppm/K	± 0.25 %	201 6...	216 6...	206 6...	-	-
		± 0.1 %	201 7...	216 7...	206 7...	-	-
	± 15 ppm/K	± 0.25 %	202 6...	217 6...	207 6...	-	-
		± 0.1 %	202 7...	217 7...	207 7...	-	-
	± 10 ppm/K	± 0.25 %	203 6...	218 6...	208 6...	-	-
		± 0.1 %	203 7...	218 7...	208 7...	-	-
MCU 0805	± 25 ppm/K	± 0.25 %	241 6...	256 6...	246 6...	-	-
		± 0.1 %	241 7...	256 7...	246 7...	-	-
	± 15 ppm/K	± 0.25 %	242 6...	257 6...	247 6...	-	-
		± 0.1 %	242 7...	257 7...	247 7...	-	-
	± 10 ppm/K	± 0.25 %	243 6...	258 6...	248 6...	-	-
		± 0.1 %	243 7...	258 7...	248 7...	-	-
MCA 1206	± 25 ppm/K	± 0.25 %	381 6...	396 6...	386 6...	-	-
		± 0.1 %	381 7...	396 7...	386 7...	-	-
	± 15 ppm/K	± 0.25 %	382 6...	397 6...	387 6...	-	-
		± 0.1 %	382 7...	397 7...	387 7...	-	-
	± 10 ppm/K	± 0.25 %	383 6...	398 6...	388 6...	-	-
		± 0.1 %	383 7...	398 7...	388 7...	-	-



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.