

## Metal Film Resistors, Military, MIL-R-10509 Qualified, Precision, Type RN and MIL-PRF-22684 Qualified, Type RL


**FEATURES**

- Very low noise (- 40 dB)
- Very low voltage coefficient (5 ppm/V)
- Controlled temperature coefficient
- Flame retardant epoxy coating
- Commercial alternatives to military styles are available with higher power ratings. See CMF Industrial data sheet: [www.vishay.com/doc?31018](http://www.vishay.com/doc?31018)

| STANDARD ELECTRICAL SPECIFICATIONS |           |                 |   |  |  |  |   |   |   |                                 |                                 |
|------------------------------------|-----------|-----------------|---|--|--|--|---|---|---|---------------------------------|---------------------------------|
| GLOBAL MODEL                       | MIL STYLE | MIL SPEC. SHEET | POWER RATING<br>$P_{70^{\circ}\text{C}}$<br>W | POWER RATING<br>$P_{125^{\circ}\text{C}}$<br>W | MAX. WORKING VOLTAGE <sup>(1)</sup><br>V | RESISTANCE RANGE<br>$\Omega$<br>MIL-R-10509<br>$\pm 100 \text{ ppm}/^{\circ}\text{C}$<br>(D) | RESISTANCE RANGE<br>$\Omega$<br>MIL-R-10509<br>$\pm 50 \text{ ppm}/^{\circ}\text{C}$<br>(C) | RESISTANCE RANGE<br>$\Omega$<br>MIL-R-10509<br>$\pm 25 \text{ ppm}/^{\circ}\text{C}$<br>(E) | RESISTANCE RANGE<br>$\Omega$<br>MIL-PRF-22684 | TOL. <sup>(3)</sup><br>$\pm \%$ | DIELECTRIC STRENGTH<br>$V_{AC}$ |
| CMF50                              | RN50      | 08              | -   | 0.05   | 200                                      | -  | 10 to 100K  | 10 to 100K  | -   | 0.1, 0.25, 0.5, 1               | 450                             |
| CMF55                              | RN55      | 07              | 0.125   | 0.10   | 200                                      | 10 to 301K   | 49.9 to 100K  | 49.9 to 100K  | -   | 0.1, 0.25, 0.5, 1               | 450                             |
| CMF60                              | RN60      | 01              | 0.25  | 0.125  | 300                                      | 10 to 1M   | 49.9 to 499K  | 49.9 to 499K  | -   | 0.1, 0.25, 0.5, 1               | 500                             |
| CMF65                              | RN65      | 02              | 0.50  | 0.25   | 350                                      | 10 to 2M   | 49.9 to 1M  | 49.9 to 1M  | -   | 0.1, 0.25, 0.5, 1               | 900                             |
| CMF70                              | RN70      | 03              | 0.75 <sup>(2)</sup>                           | 0.50   | 500                                      | 10 to 2.49M  | 24.9 to 1M  | 24.9 to 1M  | -   | 0.1, 0.25, 0.5, 1               | 900                             |
| CMF07                              | RL07      | 01              | 0.25  | -  | 250                                      | -  | -   | -   | 51 to 150K                                    | 2, 5                            | 450                             |
| CMF20                              | RL20      | 02              | 0.50  | -  | 350                                      | -  | -   | -   | 4.3 to 470K                                   | 2, 5                            | 700                             |

**Notes**

- (1) Continuous working voltage shall be  $\sqrt{P \times R}$  or maximum working voltage, whichever is less.
- (2) Formerly rated at 1 W and is the direct replacement for RN70 of MIL-R-10509 rev. D.
- (3) Tolerances of  $\pm 0.1 \%$ ,  $\pm 0.25 \%$  and  $\pm 0.5 \%$  are not applicable to characteristic D.

| TECHNICAL SPECIFICATIONS    |                    |   |
|-----------------------------|--------------------|---|
| PARAMETER                   | UNIT               | CONDITION   |
| Voltage Coefficient         | ppm/V              | 5 when measured between 10 % and full rated voltage   |
| Insulation Resistance       | W                  | $\geq 10^{10}$ min. dry; $\geq 10^8$ min. after moisture test                                 |
| Operating Temperature Range | $^{\circ}\text{C}$ | - 65/+ 175 (see derating curves for military range)   |
| Terminal Strength           | lb                 | 5 pound pull test for RL07/RL20; 2 pound pull test for all others                             |
| Solderability               |                    | Continuous satisfactory coverage when tested in accordance with MIL-R-10509 and MIL-PRF-22684 |



**GLOBAL PART NUMBER INFORMATION**

New Global Part Numbering: RN60D3483FR36 (preferred part numbering format)

R N 6 0 D 3 4 8 3 F R 3 6

| MIL STYLE                            | CHARACTERISTIC                          | RESISTANCE VALUE  | TOLERANCE CODE  | PACKAGING  | SPECIAL   |
|--------------------------------------|---|---|---|--|---|
| RN50<br>RN55<br>RN60<br>RN65<br>RN70 | E = 25 ppm<br>C = 50 ppm<br>D = 100 ppm | 3 digit significant figure, followed by a multiplier<br>Use "R" for values < 100 Ω<br>10R0 = 10 Ω<br>2152 = 21.5 kΩ<br>2494 = 2.49 MΩ | B = ± 0.1 %<br>C = ± 0.25 %<br>D = ± 0.5 %<br>F = ± 1 % | B14 = Tin/lead, bulk<br>BSL = Tin/lead, bulk, single lot date code<br>R36 = Tin/lead, T/R (full)<br>RE6 = Tin/lead, T/R (1000 pieces)<br>RSL = Tin/lead, T/R, single lot date code | Blank = Standard (Dash number)<br>88 = Hot solder dip<br>143 = Non-magnetic |

Historical Part Number example: RN60D3483F (will continue to be accepted)

|           |                |                  |                |           |
|-----------|----------------|------------------|----------------|-----------|
| RN60      | D              | 3483             | F              | R36       |
| MIL STYLE | CHARACTERISTIC | RESISTANCE VALUE | TOLERANCE CODE | PACKAGING |

New Global Part Numbering: RL07S471JR36 (preferred part numbering format)

R L 0 7 S 4 7 1 J R 3 6

| MIL STYLE    | LEAD MATERIAL  | RESISTANCE VALUE   | TOLERANCE CODE         | PACKAGING  | SPECIAL   |
|--------------|----------------|--|------------------------|--|---|
| RL07<br>RL20 | S = Solderable | 2 digit significant figure, followed by a multiplier<br>Use "R" for values < 10 Ω<br>4R3 = 4.3 Ω<br>202 = 2.0 kΩ<br>474 = 470 kΩ | G = ± 2 %<br>J = ± 5 % | B14 = Tin/lead, bulk<br>BSL = Tin/lead, bulk, single lot date code<br>R36 = Tin/lead, T/R (full)<br>RE6 = Tin/lead, T/R (1000 pieces)<br>RSL = Tin/lead, T/R, single lot date code | Blank = Standard (Dash number)<br>88 = Hot solder dip<br>143 = Non-magnetic |

Historical Part Number example: RL07S471J (will continue to be accepted)

|           |               |                  |                |           |
|-----------|---------------|------------------|----------------|-----------|
| RL07      | S             | 471              | J              | R36       |
| MIL STYLE | LEAD MATERIAL | RESISTANCE VALUE | TOLERANCE CODE | PACKAGING |

**Note**

- For additional information on packaging, refer to the Through Hole Resistor Packaging document ([www.vishay.com/doc?31544](http://www.vishay.com/doc?31544)).

| MATERIAL SPECIFICATIONS |  |
|-------------------------|--|
| Element                 | Nickel-chrome alloy  |
| Coating                 | Flame retardant epoxy, formulated for superior moisture protection       |
| Core                    | Fire-cleaned high purity ceramic   |
| Termination             | Standard lead material is solder-coated copper. Solderable and weldable. |

**CAGE CODE: 91637**

**APPLICABLE MIL-SPECS**


**MIL-R-10509 and MIL-PRF-22684:** The CMF models meet or exceed the electrical, environmental and dimensional requirements of MIL-R-10509 and MIL-PRF-22684.

**Noise:** Vishay Dale metal film resistors have exceptionally low noise level. Average for standard resistance range is 0.10 μV per V over a decade of frequency, with low and intermediate resistance values typically below 0.05 μV per V.

| ENVIRONMENTAL SPECIFICATIONS |   |
|------------------------------|---|
| General                      | Environmental performance is shown in the Environmental Performance table. Test methods are those specified in MIL-R-10509 and MIL-PRF-22684. |
| Shelf Life                   | Resistance shifts due to storage at room temperature are negligible.  |




Vishay Dale CMF resistors have an operating temperature range of - 65 °C to + 175 °C. They must be derated according to the following curves:



### DERATING

### DIMENSIONS in inches (millimeters)



| VISHAY DALE MODEL | A                               | B                              | C (MAX.)                       | D                              |
|-------------------|---------------------------------|--------------------------------|--------------------------------|--------------------------------|
| CMF50             | 0.150 ± 0.020<br>(3.81 ± 0.51)  | 0.065 ± 0.015<br>(1.65 ± 0.38) | 0.244<br>(6.20)                | 0.016 ± 0.002<br>(0.41 ± 0.05) |
| CMF55             | 0.240 ± 0.020<br>(6.10 ± 0.51)  | 0.090 ± 0.008<br>(2.29 ± 0.20) | 0.278<br>(7.06) <sup>(1)</sup> | 0.025 ± 0.002<br>(0.64 ± 0.05) |
| CMF60             | 0.344 ± 0.031<br>(8.74 ± 0.79)  | 0.145 ± 0.015<br>(3.68 ± 0.38) | 0.425<br>(10.80)               | 0.025 ± 0.002<br>(0.64 ± 0.05) |
| CMF65             | 0.562 ± 0.031<br>(14.27 ± 0.79) | 0.180 ± 0.015<br>(4.57 ± 0.38) | 0.687<br>(17.45)               | 0.025 ± 0.002<br>(0.64 ± 0.05) |
| CMF70             | 0.562 ± 0.031<br>(14.27 ± 0.79) | 0.180 ± 0.015<br>(4.57 ± 0.38) | 0.687<br>(17.45)               | 0.032 ± 0.002<br>(0.81 ± 0.05) |
| CMF07             | 0.240 ± 0.020<br>(6.10 ± 0.51)  | 0.090 ± 0.008<br>(2.29 ± 0.20) | 0.278<br>(7.06)                | 0.025 ± 0.002<br>(0.64 ± 0.05) |
| CMF20             | 0.375 ± 0.040<br>(9.53 ± 1.02)  | 0.145 ± 0.015<br>(3.68 ± 0.38) | 0.425<br>(10.80)               | 0.032 ± 0.002<br>(0.81 ± 0.05) |

#### Notes

- <sup>(1)</sup> 0.290" (7.37) for ± 0.25 % and ± 0.1 % resistance tolerances.
- <sup>(2)</sup> Lead length for product in bulk pack. For product supplied in Tape and Reel, the actual lead length would be based on the body size, tape spacing and lead trim.

| MILITARY POWER RATING |                    |                       |               |
|-----------------------|--------------------|-----------------------|---------------|
| WATTAGE               | MILITARY QUALIFIED |                       |               |
|                       | MIL-R-10509        |                       | MIL-PRF-22684 |
|                       | AT + 70 °C (D)     | AT + 125 °C (C and E) | AT + 70 °C    |
| 0.05                  | -                  | RN50                  | -             |
| 0.10                  | -                  | RN55                  | -             |
| 0.125                 | RN55               | RN60                  | -             |
| 0.25                  | RN60               | RN65                  | RL07          |
| 0.50                  | RN65               | RN70                  | RL20          |
| 0.75 <sup>(3)</sup>   | RN70               | -                     | -             |

#### Notes

- Commercial equivalents of military styles are available with higher power ratings. Consult factory.
- <sup>(3)</sup> Formerly rated at 1 W and is the direct replacement for RN70 of MIL-R-10509 rev. D.



| MARKING (per MIL-PRF-10509)   |                                       |
|---|---------------------------------------|
| Characteristics: D = 100 ppm, C = 50 ppm, E = 25 ppm<br>Tolerance: F = 1 %, D = 0.5 %, C = 0.25 %, B = 0.1 %<br>Value = Three significant figures and multiplier<br>J = JAN (Joint Army - Navy) brand |                                       |
| RN50: (3 lines)   | RN55, RN60, RN65, RN70 (4 lines)      |
| J50D JAN, type, characteristic  | DALE Company logo                     |
| 1211 Value  | 0137J 4 digit date code and JAN brand |
| F137 Tolerance and 3 digit date code  | RN55D Type and characteristic         |
|   | 1211F Value and Tolerance             |

**Note**

- RL series are color banded per MIL-PRF-22684.

| PERFORMANCE                                    |                           |                           |                           |                           |
|--|---------------------------|---------------------------|---------------------------|---------------------------|
| REQUIREMENT                                    | MIL-R-10509               |                           |                           | MIL-PRF-22684             |
|  | CHARACTERISTIC D          | CHARACTERISTIC C          | CHARACTERISTIC E          |                           |
| MIL Temperature Coefficient                    | + 200 ppm/°C - 500 ppm/°C | ± 50 ppm/°C               | ± 25 ppm/°C               | ± 200 ppm/°C              |
| Applicable Vishay Dale Temperature Coefficient | ± 100 ppm/°C              | ± 50 ppm/°C               | ± 25 ppm/°C               | ± 200 ppm/°C              |
| <b>TEST</b>                                    | <b>MIL<sub>max.</sub></b> | <b>MIL<sub>max.</sub></b> | <b>MIL<sub>max.</sub></b> | <b>MIL<sub>max.</sub></b> |
| Thermal Shock                                  | ± 0.50 % ΔR               | ± 0.25 % ΔR               | ± 0.25 % ΔR               | ± 1.00 % ΔR               |
| Short Time Overload                            | ± 0.50 % ΔR               | ± 0.25 % ΔR               | ± 0.25 % ΔR               | ± 0.50 % ΔR               |
| Low Temperature Operation                      | ± 0.50 % ΔR               | ± 0.25 % ΔR               | ± 0.25 % ΔR               | ± 0.50 % ΔR               |
| Moisture Resistance                            | ± 1.50 % ΔR               | ± 0.50 % ΔR               | ± 0.50 % ΔR               | ± 1.50 % ΔR               |
| Shock  | ± 0.50 % ΔR               | ± 0.25 % ΔR               | ± 0.25 % ΔR               | ± 0.50 % ΔR               |
| Vibration                                      | ± 0.50 % ΔR               | ± 0.25 % ΔR               | ± 0.25 % ΔR               | ± 0.50 % ΔR               |
| Load Life                                      | ± 1.00 % ΔR               | ± 0.50 % ΔR               | ± 0.50 % ΔR               | ± 2.00 % ΔR               |
| Dielectric Withstanding Voltage                | ± 0.50 % ΔR               | ± 0.25 % ΔR               | ± 0.25 % ΔR               | ± 0.50 % ΔR               |
| Effect of Solder                               | ± 0.50 % ΔR               | ± 0.10 % ΔR               | ± 0.10 % ΔR               | ± 0.50 % ΔR               |



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.**