


Metal Film Resistors, Military/Established Reliability, MIL-PRF-55182 Qualified, Precision, Type RNC, Characteristics J, H, K



FEATURES

- Meets requirements of MIL-PRF-55182
- Very low noise (- 40 dB)
- Verified failure rate (contact factory for current level)
- 100 % stabilization and screening tests. Group A testing, if desired, to customer requirements
- Controlled temperature coefficient
- Epoxy coating provides superior moisture protection
- Standard lead on RNC product is solderable and weldable
- Traceability of materials and processing
- Monthly acceptance testing
- Vishay Dale has complete capability to develop specific reliability programs designed to customer requirements
- Extensive stocking program at distributors and factory on RNC50, RNC55, RNC60 and RNC65
- For MIL-PRF-55182 characteristics E and C product, see Vishay Angstrom's HDN (Military RNR/RNN) datasheet

| STANDARD ELECTRICAL SPECIFICATIONS | | | | | | | | | | |
|------------------------------------|---------------------|-----------------|-------------------------|--------------------------|----------------------|----------------------------------|-----------------------|--------------------|--------------------|-----------------------|
| VISHAY DALE MODEL | MIL-PRF-55182 STYLE | MIL SPEC. SHEET | POWER RATING | | TOLERANCE (4) ± % | MAXIMUM WORKING VOLTAGE (2) V | RESISTANCE RANGE Ω | | | LIFE FAILURE RATE (1) |
| | | | P _{70 °C} W | P _{125 °C} W | | | ± 100 ppm/°C (K) | ± 50 ppm/°C (H) | ± 25 ppm/°C (J) | |
| ERC50, ERC50..31 (3) | RNC50, RNR50 | 07 | 0.10 | 0.05 | 0.1, 0.5, 1 | 200 | 10 to 796K | | | M, P, R, S |
| ERC55, ERC55..65 (3) | RNC55, RNR55 | 01 | 0.125 | 0.10 | 0.1, 0.5, 1 | 200 | 10 to 2M | | | M, P, R, S |
| ERC55..200, ERC55..201 (3) | RNC60, RNR60 | 03 | 0.25 | 0.125 | 0.1, 0.5, 1 | 250 | 10 to 2M | | | M, P, R, S |
| | | | | | | | 2.01M to 3.01M | | | M |
| ERC65, ERC65..65 (3) | RNC65, RNR65 | 05 | 0.50 | 0.25 | 0.1, 0.5, 1 | 300 | 10 to 3.01M | | | M, P, R |
| ERC70 ERC70..4 (3) | RNC70, RNR70 | 06 | 0.75 | 0.50 | 0.1, 0.5, 1 | 350 | 10 to 3.01M | | | M, P, R |

Notes


- (1) Consult factory for current QPL failure rates.
 (2) Continuous working voltage shall be $\sqrt{P \times R}$ or maximum working voltage, whichever is less.
 (3) Hot solder dipped leads
 (4) Standard resistance tolerances: ± 0.1 % (B), ± 0.5 % (D) and ± 1 % (F). ± 0.1 % not applicable to characteristic K.

| TECHNICAL SPECIFICATIONS | | |
|-----------------------------|-----------------|-----------------------------------------------------------------------------------------|
| PARAMETER | UNIT | CONDITION |
| Voltage Coefficient, max. | ppm/V | 5/V when measured between 10 % and full rated voltage |
| Dielectric Strength | V _{AC} | RNC50, RNC55 and RNC60 = 450; RNC65 and RNC70 = 900 |
| Insulations Resistance | Ω | ≥ 10 ¹¹ dry; ≥ 10 ⁹ after moisture test |
| Operating Temperature Range | °C | - 65 to + 175 |
| Terminal Strength | lb | 2 lb pull test on RNC50, RNC55, RNC60 and RNC65; 4.5 lb pull test on RNC70 |
| Solderability | | Continuous satisfactory coverage when tested in accordance with MIL-STD-202, Method 208 |
| Weight | g | RNC50 = 0.11; RNC55 = 0.35; RNC60 = 0.35; RNC65 = 0.84; RNC70 = 1.60 |



| GLOBAL PART NUMBER INFORMATION | | | | | | |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------|---------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| New Global Part Numbering: RNC55H2152FRR36 (preferred part numbering format) | | | | | | |
| <div style="display: flex; justify-content: space-around; font-weight: bold; font-size: 1.2em;"> RNC55H2152FRR36 </div> | | | | | | |
| MIL STYLE | CHARACTERISTICS | RESISTANCE VALUE | TOLERANCE CODE | FAILURE RATE | PACKAGING | SPECIAL |
| RNC = Solderable/weldable RNR = Solderable only (see Standard Electrical Specifications table) | J = ± 25 ppm H = ± 50 ppm K = ± 100 ppm | 3 digit significant figure, followed by a multiplier Use "R" for values < 100 Ω 10R0 = 10 Ω 2152 = 21.5 kΩ 3014 = 3.01 MΩ | B = ± 0.1 % D = ± 0.5 % F = ± 1 % | M = 1.0%/1000 h P = 0.1%/1000 h R = 0.01%/1000 h S = 0.001%/1000 h | B14 = Tin/lead, bulk BSL = Tin/lead, bulk, single lot date code R36 = Tin/lead, T/R (full; 50, 55, 60) R64 = Tin/lead, T/R (full; 65, 70) RE6 = Tin/lead, T/R (1000 pieces) RSL = Tin/lead, T/R, single lot date code | Blank = Standard (Dash number) (Up to 3 digits) From 1 to 999 as applicable 4 = Hot solder dip (70's) 31 = Hot solder dip (50's) 65 = Hot solder dip (55's, 65's) 201 = Hot solder dip (60's) |
| Historical Part Number example: RNC55H2152FR R36 (will continue to be accepted) | | | | | | |
| RNC55 | H | 2152 | F | R | R36 | |
| MIL STYLE | CHARACTERISTIC | RESISTANCE VALUE | TOLERANCE CODE | FAILURE RATE | PACKAGING | |

DIMENSIONS in inches (millimeters)



Note
 (1) 1.08 ± 0.125 (27.43 ± 3.18) if tape and reel

| VISHAY DALE MODEL | MIL-PRF-55182 STYLE | A | B | C (Max.) | D | E |
|-------------------|---------------------|-----------------------------------------------|--------------------------------|------------------|--------------------------------|--------------------------------|
| ERC50 | RNC50, RNR50 | 0.150 ± 0.020 (3.81 ± 0.51) | 0.070 ± 0.010 (1.78 ± 0.25) | 0.187 (4.75) | 0.016 ± 0.002 (0.41 ± 0.05) | 1.25 ± 0.266 (31.75 ± 6.76) |
| ERC55 | RNC55, RNR55 | 0.250 + 0.031 - 0.046 (6.35 + 0.79 - 1.17) | 0.094 ± 0.012 (2.39 ± 0.30) | 0.300 (7.62) | 0.025 ± 0.002 (0.64 ± 0.05) | 1.50 ± 0.125 (38.1 ± 3.18) |
| ERC55..200 | RNC60, RNR60 | 0.280 ± 0.020 (7.11 ± 0.51) | 0.097 ± 0.012 (2.46 ± 0.30) | 0.350 (8.89) | 0.025 ± 0.002 (0.64 ± 0.05) | 1.50 ± 0.125 (38.1 ± 3.18) |
| ERC65 | RNC65, RNR65 | 0.562 ± 0.031 (14.27 ± 0.79) | 0.180 ± 0.015 (4.57 ± 0.38) | 0.687 (17.45) | 0.025 ± 0.002 (0.64 ± 0.05) | 1.50 ± 0.125 (38.1 ± 3.18) |
| ERC70 | RNC70, RNR70 | 0.562 ± 0.031 (14.27 ± 0.79) | 0.180 ± 0.015 (4.57 ± 0.38) | 0.687 (17.45) | 0.032 ± 0.002 (0.81 ± 0.05) | 1.50 ± 0.125 (38.1 ± 3.18) |

| MATERIAL SPECIFICATIONS | |
|-------------------------|-------------------------------------------------------------------------------------------------|
| Element | Vacuum-deposited nickel-chrome alloy |
| Core | Fire-cleaned high purity ceramic |
| Encapsulation | Specially formulated epoxy compound |
| Termination | Standard lead material is solder-coated copper Solderable and weldable per MIL-STD-1276, Type C |

APPLICABLE MIL-SPECIFICATIONS

MIL-PRF-55182:

The ERC series meets the electrical, environmental and dimensional requirements of MIL-PRF-55182.

MIL-R-10509:

MIL-PRF-55182 supercedes MIL-R-10509 on new designs. The ERC series meets or exceeds MIL-R-10509 requirements.

Documentation:

Qualification and failure rate verification test data is maintained by Vishay Dale and is available upon request. Lot traceability and identification data is maintained by Vishay Dale for five years.



POWER RATING

Power ratings are based on the following two conditions:

- ± 2.0 % maximum ΔR in 10 000 h load life
- + 175 °C maximum operating temperature

CAGE CODE: 91637

Vishay Dale ERC resistors have an operating temperature range of - 65 °C to + 175 °C. They must be derated according to the following curve:



MARKING

- Per MIL-PRF-55182



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.