


- Features:
- Precision tolerances to $\pm 0.01\%$
 - TCR down to $\pm 5\text{ppm}/^\circ\text{C}$
 - Wide R-value range
 - Consult factory for tighter tolerances
 - 2010 and 2512 sizes now available
 - RoHS compliant



Electrical Specifications											
Type / Code	Old Pkg Code	Power Rating (Watts) @ 70°C	Maximum Working Voltage(1)	Maximum Overload Voltage	Resistance Temperature Coefficient	Ohmic Range (Ω) and Tolerance					
						0.01%	0.05%	0.1%	0.25%	0.5%	1%
RNCF0201	05	0.032W (0.05W(2))	15V	30V	$\pm 25\text{ ppm}/^\circ\text{C}$ $\pm 50/100\text{ ppm}/^\circ\text{C}$	-	-	-	-	49.9 - 5K 49.9 - 33K	49.9 - 5K 49.9 - 33K
RNCF0402	10	0.063W	25V	50V	$\pm 5\text{ ppm}/^\circ\text{C}$ $\pm 10\text{ ppm}/^\circ\text{C}$ $\pm 15\text{ ppm}/^\circ\text{C}$ $\pm 25\text{ ppm}/^\circ\text{C}$ $\pm 50/100\text{ ppm}/^\circ\text{C}$	49.9 - 5K 49.9 - 12K 49.9 - 12K -	49.9 - 5K 49.9 - 12K -	49.9 - 5K 10 - 100K 49.9 - 70K 10 - 205K 10 - 205K	- 10 - 100K -	10 - 100K -	10 - 100K -
RNCF0603	16	0.063W (0.1W(2))	50V	100V	$\pm 5\text{ ppm}/^\circ\text{C}$ $\pm 10\text{ ppm}/^\circ\text{C}$ $\pm 15\text{ ppm}/^\circ\text{C}$ $\pm 25\text{ ppm}/^\circ\text{C}$ $\pm 50/100\text{ ppm}/^\circ\text{C}$	24.9 - 15K 24.9 - 100K 24.9 - 100K -	24.9 - 15K 4.7 - 332K -	24.9 - 15K 4.7 - 390K 4.7 - 332K 4.7 - 1M 4.7 - 1M	- 10 - 390K -	10 - 390K -	10 - 390K -
RNCF0805	20	0.1W (0.125W(2))	100V	200V	$\pm 5\text{ ppm}/^\circ\text{C}$ $\pm 10\text{ ppm}/^\circ\text{C}$ $\pm 15\text{ ppm}/^\circ\text{C}$ $\pm 25\text{ ppm}/^\circ\text{C}$ $\pm 50/100\text{ ppm}/^\circ\text{C}$	24.9 - 30K 24.9 - 200K 24.9 - 200K -	24.9 - 30K 4.7 - 511K -	24.9 - 30K 4.7 - 800K 4.7 - 511K 4.7 - 2M 4.7 - 2M	- 10 - 800K -	10 - 800K -	10 - 800K -
RNCF1206	32	0.125W (0.25W(2))	150V	300V	$\pm 5\text{ ppm}/^\circ\text{C}$ $\pm 10\text{ ppm}/^\circ\text{C}$ $\pm 15\text{ ppm}/^\circ\text{C}$ $\pm 25\text{ ppm}/^\circ\text{C}$ $\pm 50/100\text{ ppm}/^\circ\text{C}$	24.9 - 50K 24.9 - 500K 24.9 - 500K -	24.9 - 50K 4.7 - 1M -	24.9 - 50K 4.7 - 1M 4.7 - 1M 4.7 - 2.5M 4.7 - 2.5M	- 10 - 1M -	10 - 1M -	10 - 1M -
RNCF1210	50	0.2W (0.25W(2))	150V	300V	$\pm 5\text{ ppm}/^\circ\text{C}$ $\pm 10\text{ ppm}/^\circ\text{C}$ $\pm 15\text{ ppm}/^\circ\text{C}$ $\pm 25\text{ ppm}/^\circ\text{C}$ $\pm 50/100\text{ ppm}/^\circ\text{C}$	24.9 - 50K 24.9 - 500K 24.9 - 500K -	24.9 - 50K 4.7 - 1M -	24.9 - 50K 4.7 - 1M 4.7 - 1M 4.7 - 2.5M 4.7 - 2.5M	- -	1 - 2.5M 1 - 2.5M	1 - 2.5M 1 - 2.5M
RNCF2010	57	0.25W (0.5W(2))	150V	300V	$\pm 5\text{ ppm}/^\circ\text{C}$ $\pm 10\text{ ppm}/^\circ\text{C}$ $\pm 15\text{ ppm}/^\circ\text{C}$ $\pm 25\text{ ppm}/^\circ\text{C}$ $\pm 50/100\text{ ppm}/^\circ\text{C}$	24.9 - 100K 24.9 - 500K 24.9 - 500K -	24.9 - 100K 4.7 - 1M -	24.9 - 100K 4.7 - 1M 4.7 - 1M 4.7 - 3M 4.7 - 3M	- -	1 - 3M 1 - 3M	1 - 3M 1 - 3M
RNCF2512	63	0.5W (1W(2))	150V	300V	$\pm 5\text{ ppm}/^\circ\text{C}$ $\pm 10\text{ ppm}/^\circ\text{C}$ $\pm 15\text{ ppm}/^\circ\text{C}$ $\pm 25\text{ ppm}/^\circ\text{C}$ $\pm 50/100\text{ ppm}/^\circ\text{C}$	24.9 - 100K 24.9 - 500K 24.9 - 500K -	24.9 - 100K 4.7 - 1M -	24.9 - 100K 4.7 - 1M 4.7 - 1M 4.7 - 3M 4.7 - 3M	- -	1 - 3M 1 - 3M	1 - 3M 1 - 3M

(1) Lesser of $\sqrt{\text{PR}}$ or maximum working voltage.

(2) Higher power rating for each package size is valid if ambient temp $\leq 80^\circ\text{C}$ and terminal temp $\leq 105^\circ\text{C}$




Mechanical Specifications						
Type / Code	L Body Length	W Body Width	H Body Height	a Top Termination	b Bottom Termination	Unit
RNCF0201	0.024 ± 0.002	0.012 ± 0.002	0.009 ± 0.001	0.005 ± 0.002	0.005 ± 0.002	inches
	0.60 ± 0.05	0.30 ± 0.05	0.23 ± 0.03	0.12 ± 0.05	0.12 ± 0.05	mm
RNCF0402	0.039 ± 0.002	0.020 ± 0.002	0.014 ± 0.002	0.008 ± 0.004	0.010 ± 0.004	inches
	1.00 ± 0.05	0.50 ± 0.05	0.35 ± 0.05	0.20 ± 0.10	0.25 ± 0.10	mm
RNCF0603	0.063 ± 0.008	0.031 ± 0.008	0.016 ± 0.006	0.012 ± 0.008	0.012 ± 0.008	inches
	1.60 ± 0.20	0.80 ± 0.20	0.40 ± 0.15	0.30 ± 0.20	0.30 ± 0.20	mm
RNCF0805	0.079 ± 0.008	0.049 ± 0.008	0.020 ± 0.006	0.016 ± 0.008	0.016 ± 0.008	inches
	2.00 ± 0.20	1.25 ± 0.20	0.50 ± 0.15	0.40 ± 0.20	0.40 ± 0.20	mm
RNCF1206	0.126 ± 0.008	0.063 ± 0.008	0.020 ± 0.006	0.020 ± 0.012	0.016 ± 0.008	inches
	3.20 ± 0.20	1.60 ± 0.20	0.50 ± 0.15	0.50 ± 0.30	0.40 ± 0.20	mm
RNCF1210	0.122 ± 0.008	0.094 ± 0.006	0.024 ± 0.004	0.020 ± 0.012	0.016 ± 0.008	inches
	3.10 ± 0.20	2.40 ± 0.15	0.60 ± 0.10	0.50 ± 0.30	0.40 ± 0.20	mm
RNCF2010	0.193 ± 0.006	0.094 ± 0.006	0.024 ± 0.004	0.024 ± 0.012	0.020 ± 0.010	inches
	4.90 ± 0.15	2.40 ± 0.15	0.60 ± 0.10	0.60 ± 0.30	0.50 ± 0.25	mm
RNCF2512	0.248 ± 0.006	0.122 ± 0.006	0.024 ± 0.004	0.024 ± 0.012	0.020 ± 0.010	inches
	6.30 ± 0.15	3.10 ± 0.15	0.60 ± 0.10	0.60 ± 0.30	0.50 ± 0.25	mm

Performance Characteristics					
Test	Specification	Specification for Tolerances = 0.01%	Specification for Tolerances = 0.05%	Typical	Test Method
Moisture Resistance, Thermal Shock	$\Delta R \pm (0.25\% + 0.05\Omega)$	$\Delta R \pm 0.01\%$	$\Delta R \pm 0.05\%$	$\leq 0.1\%$	-55°C - 150°C, 100 cycles
Load Life	$\Delta R \pm (0.2\% + 0.05\Omega)$	$\Delta R \pm 0.01\%$	$\Delta R \pm 0.05\%$	$\leq 0.2\%$	70±2°C, Maximum working voltage for 1000 hrs with 1.5 hrs ON and 0.5 hrs OFF
	$>7K\Omega \Delta R \pm 0.5\%$ $\Delta R \pm 0.5\%$ for high power rating				
Load Life in Moisture	$\Delta R \pm (0.3\% + 0.05\Omega)$	$\Delta R \pm 0.01\%$	$\Delta R \pm 0.05\%$	$\leq 0.25\%$	40±2°C, 90-95% RH Maximum working voltage for 1000 hrs with 1.5 hrs ON and 0.5 hrs OFF
	$\Delta R \pm 0.5\%$ for high power rating				
Resistance to Soldering Heat	$\Delta R \pm (0.2\% + 0.05\Omega)$	$\Delta R \pm 0.01\%$	$\Delta R \pm 0.05\%$	$\leq 0.5\%$	260±5°C for 10 seconds
Solderability	Min 95% coverage			$\geq 0.95\%$	245±5°C for 3 seconds
Bending Strength	$\Delta R \pm (0.2\% + 0.05\Omega)$	$\Delta R \pm 0.01\%$	$\Delta R \pm 0.05\%$	$\leq 0.05\%$	Bending amplitude 3mm for 10 seconds
Dielectric Withstanding Voltage	by type			$\leq 0.05\%$	Maximum overload voltage for 1 minute
Short Time Overload	$\Delta R \pm (0.2\% + 0.05\Omega)$	$\Delta R \pm 0.01\%$	$\Delta R \pm 0.05\%$	$\leq 0.05\%$	RCWV*2.5 or Maximum overload voltage for 5 seconds
Insulation Resistance	$>1G\Omega$			$\geq 1G\Omega$	Apply 100V _{DC} for 1 minute
Low Temperature Operation	$\Delta R \pm 0.2\%$	$\Delta R \pm 0.01\%$	$\Delta R \pm 0.05\%$		1 hour, -65°C, followed by 45 minutes of RCWV
	$\Delta R \pm 0.5\%$ for high power rating				

Operating Temperature Range: -55°C to +125°C (0201); -55°C to +155°C (0402 to 2512)
Reference Standards: MIL-STD-202, JIS-C 5201-1

Power Derating Curve:



How to Order

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
R	N	C	F	0	8	0	5	D	T	E	4	K	7	5

Product Series		Size	Power	Tolerance			Packaging				TCR		Resistance Value (2)	
RNCF	Precision Thin Film Chip Resistors	0201	0.032W	Code	Tol	Value (1)	T	7" Reel Paper Tape	Size	0201, 0402	Quantity	Code	ppm	Four characters with the multiplier used as the decimal holder. 24.9 ohm = 24R9 10 Kohm = 10K0 1 Mohm = 1M00
		0402	0.063W	T	0.01%	E192, E96, E24				0603, 0805				
		0603	0.063W	A	0.05%				1206, 1210	4,000	T	10		
		0805	0.1W	B	0.1%				2010, 2512	1,000	S	15		
		1206	0.125W	C	0.25%		K	7" Reel Paper Tape	0603, 0805, 1206	1,000	E	25		
		1210	0.2W	D	0.5%	2010, 2512			1,000		C	50		
		2010	0.25W	F	1%	E96, E24			1,000		D	100		
		2512	0.5W											

(1) E192 values are not marked, and may be subject to 20Kpc MOQ
 (2) Values below 10 ohm and above 1 Mohm may be subject to 20Kpc MOQ

Legacy Part Number (before January 3, 2011):

SEI Type		Code			TCR	Nominal Resistance (2)	Tolerance		Packaging			
RNCF		20			T9	4.75K	0.5%		R			
Type	Description	Code	Wattage	Size	TCR	Tol	Values (1)		SEI Types	Pkg Qty	Code	Description
RNCF	Precision Thin Film Chip Resistor	05	0.032W	0201	T1	0.01%	E192, E96, E24		0201, 0402	10,000	R	7" reel paper tape
		10	0.063W	0402	T2	0.05%			0603, 0805,	5,000	R	
		16	0.063W	0603	T9	0.1%			1206	1,000	I	
		20	0.1W	0805	TD	0.25%			1210	5,000	R	
		32	0.125W	1206	TB	0.5%			2010, 2512	4,000	R	
		50	0.2W	1210	TA	1%				1,000	I	
		57	0.25W	2010								
		63	0.5W	2512								

(1) E192 values are not marked, and may be subject to 20Kpc MOQ
 (2) Values below 10 ohm and above 1 Mohm may be subject to 20Kpc MOQ