


Enamelled Wirewound Power Resistors Axial Leads



FEATURES

- High dissipation up to 30 W (25 °C)
- Fire proof
- Excellent endurance typical drift $\pm 1.5\%$ after 1000 h
- Conformal vitreous enamel
- All welded construction
- Low ohmic values 0.1 Ω available
- Termination: Sn/Ag/Cu




As a result of more than 50 years of experience and continuous improvements the RWM Series of resistors features proven reliability in AC or DC applications. The high quality of the RWM resides mainly in the use of a proprietary VISHAY SFERNICE enamel fired at high temperature and free from any compound liable to corrode the resistive wire.

The performance of this series of professional resistors fully meets the requirements of the following specifications:

- NF C 83-210-001
- CECC 40201-001
- BS - CECC 40201-002

DIMENSIONS in millimeters



TECHNICAL SPECIFICATIONS												
VISHAY SFERNICE STYLES	DESIGNATIONS		POWER RATING			Ohmic Range in Relation to Tolerance $\pm 5\%$ E24 Series	Qualified Ohmic Range NF C 83-210	Limiting Element Voltage	Critical Resistance	DIMENSIONS in mm		WEIGHT in g
	CECC 40201-001	CECC 40201-002	at +70 °C	at +25 °C	With Surface Temp. $\leq +450$ °C					A	Ø B	
RWM 4 x 10	RB59	JB	2.6 W	3 W	5.5 W	0.1 Ω 10 k Ω	0.1 Ω 10 k Ω	120 V	4.8 k Ω	12 ± 1	5.5 ± 1	1
RWM 4 x 22	RB61	HB	4.5 W	5 W	7 W	0.1 Ω 16 k Ω	0.1 Ω 6.8 k Ω	300 V	-	22.1 ± 1	5.5 ± 1	2
RWM 5 x 26	RB57	-	6 W	7 W	10 W	0.1 Ω 27 k Ω	0.15 Ω 10 k Ω	350 V	18.8 k Ω	24.7 ± 1	7.4 ± 1.5	3
RWM 6 x 22	RB57	KB	6 W	7 W	10 W	0.1 Ω 39 k Ω	0.15 Ω 39 k Ω	350 V	17.5 k Ω	18 ± 1	6.5 ± 1	2.2
RWM 8 x 26	RB60	-	7 W	8 W	10 W	0.1 Ω 27 k Ω	-	500 V	-	24.7 ± 1	7.4 ± 1.5	3
RWM 6 x 34	RB60	LB	7 W	8 W	12 W	0.33 Ω 36 k Ω	0.33 Ω 15 k Ω	500 V	31 k Ω	33.7 ± 1	7.4 ± 1.5	4
RWM 8 x 34	RB58	-	9.5 W	11 W	14 W	0.33 Ω 36 k Ω	-	650 V	-	33.7 ± 1	7.4 ± 1.5	4
RWM 8 x 45	RB58	MB	9.5 W	11 W	20 W	0.47 Ω 62 k Ω	0.47 Ω 33 k Ω	650 V	38 k Ω	45.8 ± 2	9.4 ± 1.5	8
RWM 10 x 45	-	-	21 W	25 W	25 W	0.47 Ω 62 k Ω	-	800 V	25.6 k Ω	45.8 ± 2	9.4 ± 1.5	8
RWM 10 x 64	-	-	21 W	25 W	25 W	0.68 Ω 100 k Ω	-	800 V	25.6 k Ω	63.8 ± 1	9.4 ± 1.5	14
RWM 10 x 65	-	-	25.8 W	30 W	30 W	0.68 Ω 100 k Ω	-	800 V	21.3 k Ω	63.8 ± 1	9.4 ± 1.5	14

Undergoes European Quality Insurance System (CECC)



PERFORMANCE			
CECC 40201 - EN 140-201			TYPICAL DRIFTS
TESTS	CONDITIONS	REQUIREMENTS	
Short Time Overload	10 Pr during 10 s 25 °C ambient	± (2 % + 0.1 Ω)	± (0.5 % + 0.05 Ω)
Temperature Cycling	- 55 °C + 200 °C	± (1 % + 0.05 Ω)	± (0.5 % + 0.05 Ω)
Humidity (Steady State)	56 days 40 °C Ambient - R.H. 95 %	± (5 % + 0.1 Ω)	± (0.5 % + 0.05 Ω)
Terminal Strength	Tensile test: 20 N 2 successive bending 2 full rotations of 180°	± (1 % + 0.05 Ω)	± (0.1 % + 0.05 Ω)
Load Life	1000 h at Pr 90/30 cycle 25 °C ambient	± (5 % + 0.1 Ω)	± (1.5 % + 0.05 Ω)

OVERLOAD

Heavy overloads can be endured in the form of short pulses < 0.1 s. Particular requirements should be submitted to Vishay Sfernice, specifying peak voltage, cycle and environmental conditions.

RECOMMENDATIONS FOR USE

Since these components are high dissipation power resistors, customers are advised to use a high melting point solder.

For low ohmic values, the measurement becomes critical and the connecting wires resistance is to be included. The value is measured at 5 mm from the resistor body.

Group Mounting

In a still atmosphere, a distance between axes equal to five times the resistor's diameter is recommended.


Cabinet Mounting

- Unventilated box: dissipation should be reduced (see dimensional drawing).
- Forced ventilation: if conditions are appropriate, dissipation may be doubled or even trebled.
- In any case: the surface temperature at the hottest point should not exceed 450 °C.


These aspects should be considered by the end user.

ELECTRICAL SPECIFICATIONS		
Tolerance	Standard	± 5 %
	On request	± 1 % and ± 2 %
Temperature Coefficient + 75 ppm/°C typical		
Dielectric Withstanding Voltage NF EN 140000		
		500 V _{RMS} - 1 min - 10 mA
Inductance		
		non inductive (Ayrton-Perry) winding available

POWER RATING CHART



TYPICAL TEMPERATURE RISE



MARKING

Sfernice trademark, model and style, CECC style, if applicable (except for the smallest model due to lack of space: (4 x 10 or RB 59), ohmic value, resistance tolerance, manufacturing date (year - month).

ORDERING INFORMATION							
RWM	4 x 10		XXX	1U2	± 5 %	AM500	e1
MODEL	STYLE	NI OPTIONAL	SPECIAL DESIGN	OHMIC VALUE	TOLERANCE	PACKAGING	LEAD (Pb)-FREE
		Non Inductive Winding	Method N° Optional	Custom items are subject to extra charge and min. order. Please see price list.			

GLOBAL PART NUMBER INFORMATION																	
R	W	M	0	4	1	0	1	R	2	0	J	R	1	5		E	1
GLOBAL MODEL	SIZE	OPTION	OHMIC VALUE			TOLERANCE	PACKAGING	SPECIAL	LEAD (Pb)-FREE								
RWM	d x L: 0410 0422 0526 0826 0634 0845 1045 1064 1065	Blank or N (Non inductive winding)	The first three digits are significant figures and the last digit specifies the number of zeros to follow. R designates decimal point. 48R7 = 48.7 Ω 1R20 = 1.2 Ω 1002 = 10 000 Ω R330 = 0.33 Ω ...			F = 1 % G = 2 % J = 5 % K = 10 %	Size 0410, 0422, 0526, 0826, 0622: R15 = Reel (1000 pieces) Size 0845, 1045, 1064, 1065: B25 = Box (50 pieces) Size 0634: S09 = Bag (50 pieces) Other packaging existing	As applicable Ex: AD7	Sn(99), Ag(0.3), Cu(0.7): E1								



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.