


Thick Film Surface Mount Chip Resistors, Wraparound, Extremely Low Value (0.01 Ω to 0.976 Ω)


FEATURES

- Extremely low resistance values (0.01 Ω to 0.976 Ω)
- Suitable for current sensing and shunts
- Metal glaze on high quality ceramic
- Protective overglaze
- Lead (Pb)-free solder contacts on Ni barrier layer
- Compliant to RoHS Directive 2002/95/EC
- Halogen-free according to IEC 61249-2-21 definition


RoHS
COMPLIANT
HALOGEN
FREE

STANDARD ELECTRICAL SPECIFICATIONS						
GLOBAL MODEL	CASE SIZE	POWER RATING $P_{70^\circ\text{C}}$ W	TEMPERATURE COEFFICIENT \pm ppm/ $^\circ\text{C}$	RESISTANCE RANGE Ω	TOLERANCE \pm %	E-SERIES
RCWE0402	0402	0.125	400	0.033 to 0.05	5	24
			200	0.051 to 0.18	1, 5	
			100	0.2 to 0.976	1, 5	
RCWE0603	0603	0.2	700	0.010 to 0.018	5	24
			400	0.02 to 0.03	1, 5	
			200	0.033 to 0.1	1, 5	
RCWE0805	0805	0.25	100	0.11 to 0.976	1, 5	24
			400	0.010 to 0.018	5	
			300	0.02 to 0.03	1, 5	
RCWE1206	1206	0.5	200	0.033 to 0.05	1, 5	24
			100	0.051 to 0.976	1, 5	
			600	0.010 to 0.018	5	
RCWE1210	1210	1.0	300	0.02 to 0.03	1, 5	24
			200	0.033 to 0.05	1, 5	
			100	0.051 to 0.976	1, 5	
RCWE2010	2010	1.0	600	0.010 to 0.018	5	24
			300	0.02 to 0.03	1, 5	
			200	0.033 to 0.05	1, 5	
RCWE2512	2512	2.0	100	0.051 to 0.976	1, 5	24
			600	0.010 to 0.018	5	
			300	0.02 to 0.03	1, 5	
			200	0.033 to 0.05	1, 5	
			100	0.051 to 0.976	1, 5	


Notes

- Power rating depends on the max. temperature at the solder point, the component placement density and the substrate material.
- Part marking: Reference "Surface Mount Resistor Marking" (document number 20020).

GLOBAL PART NUMBER INFORMATION															
Part Number: RCWE060351L0FNEA															
R	C	W	E	0	6	0	3	5	1	L	0	F	N	E	A
GLOBAL MODEL		VALUE			TOLERANCE			TCR			PACKAGING				
RCWE0402 RCWE0603 RCWE0805 RCWE1206 RCWE1210 RCWE2010 RCWE2512		L = mΩ * R = Decimal 10L0 = 0.01 Ω R470 = 0.47 Ω Note: * Use "L" for resistance values < 0.1 Ω			F = \pm 1.0 % J = \pm 5.0 %			K = \pm 100 ppm/ $^\circ\text{C}$ N = \pm 200 ppm/ $^\circ\text{C}$ M = \pm 300 ppm/ $^\circ\text{C}$ Q = \pm 400 ppm/ $^\circ\text{C}$ P = \pm 500 ppm/ $^\circ\text{C}$ T = \pm 600 ppm/ $^\circ\text{C}$ G = \pm 700 ppm/ $^\circ\text{C}$			EA = Lead (Pb)-free, tape/reel				

TECHNICAL SPECIFICATIONS								
PARAMETER	UNIT	RCWE0402	RCWE0603	RCWE0805	RCWE1206	RCWE1210	RCWE2010	RCWE2512
Operating temperature range	°C	- 55 to + 155						
Maximum operating voltage	V	$(P \times R)^{1/2}$						
Insulation voltage U_{ins} (1 min)	V	> 75	> 100	> 200	> 300	> 300	> 300	> 300
Insulation resistance	Ω	> 10^9						
Weight/1000 pieces (typical)	g	0.7	3	5.5	10.5	17.5	26	40.5

DIMENSIONS



MODEL	DIMENSIONS in millimeters						SOLDER PAD DIMENSIONS in millimeters			
	RESISTANCE RANGE Ω	L	W	H	T1	T2	a	b	l	
RCWE0402	0.033 to 0.976	1.05 ± 0.05	0.55 ± 0.05	0.35 ± 0.1	0.3 ± 0.15	0.25 ± 0.1	0.7	0.7	0.3	
RCWE0603	0.01 to 0.03	1.6 ± 0.1	0.85 ± 0.1	0.5 ± 0.1	0.5 ± 0.2	0.3 ± 0.2	0.9	1.0	0.4	
	0.033 to 0.976				0.3 ± 0.2		0.7		0.8	
RCWE0805	0.01 to 0.03	2.0 ± 0.15	1.3 ± 0.1	0.55 ± 0.1	0.6 ± 0.2	0.35 ± 0.2	1.0	1.4	0.6	
	0.033 to 0.976				0.4 ± 0.2		0.8		1.4	1.0
RCWE1206	0.01 to 0.03	3.1 ± 0.15	1.6 ± 0.15	0.6 ± 0.1	0.9 ± 0.2	0.45 ± 0.2	1.3	1.8	1.0	
	0.033 to 0.05				0.8 ± 0.2		1.2		1.8	1.2
	0.051 to 0.976				0.45 ± 0.2		1.0		1.8	1.6
RCWE1210	0.01 to 0.03	3.1 ± 0.2	2.5 ± 0.2	0.6 ± 0.1	0.8 ± 0.2	0.4 ± 0.2	1.3	2.6	1.1	
	0.033 to 0.976				0.4 ± 0.2		0.9		2.6	2.0
RCWE2010	0.01 to 0.03	5.0 ± 0.2	2.5 ± 0.15	0.6 ± 0.1	1.6 ± 0.3	0.6 ± 0.2	2.3	3.0	1.4	
	0.033 to 0.05				0.7 ± 0.3		1.4		3.0	3.2
	0.051 to 0.976				0.7 ± 0.3		1.4		3.0	3.2
RCWE2512	0.01 to 0.03	6.3 ± 0.2	3.15 ± 0.15	0.6 ± 0.1	2.0 ± 0.3	0.6 ± 0.2	2.8	3.6	1.4	
	0.033 to 0.05				0.8 ± 0.3		1.6		3.6	3.8
	0.051 to 0.976				0.8 ± 0.3		1.6		3.6	3.8

DERATING





PERFORMANCE		
TEST	CONDITIONS OF TEST	TEST LIMITS
Thermal shock	MIL-STD-202, method 107, - 55 °C to + 125 °C, 300 cycles at each extreme	$\pm (1.0 \% + 0.0005 \Omega) \Delta R$
Short time overload	2 x rated power; duration according the model	$\pm (0.5 \% + 0.0005 \Omega) \Delta R$
High temperature exposure	MIL-STD-202, method 108, 1000 h at T = 125 °C, 0 % power	$\pm (2.0 \% + 0.0005 \Omega) \Delta R$
Temperature cycling	JESD 22, method JA-104, 1000 cycles (- 55 °C to + 125 °C)	$\pm (2.0 \% + 0.0005 \Omega) \Delta R$
Biased humidity	MIL-STD-202, method 103, 1000 h 85 °C/85 % RH, 10 % x $(P \times R)^{1/2}$	$\pm (2.0 \% + 0.0005 \Omega) \Delta R$
Mechanical shock	MIL-STD-202, method 213, condition C, 10 g's, 6 ms (half sine), 3 directions	$\pm (1.0 \% + 0.0005 \Omega) \Delta R$
Vibration	MIL-STD-202, method 204, 5 g's, 20 min, 12 cycles, 3 directions, 10 Hz to 2000 Hz	$\pm (1.0 \% + 0.0005 \Omega) \Delta R$
Operational life	MIL-STD-202, method 108, 1000 h at T = 125 °C at rated power	$\pm (2.0 \% + 0.0005 \Omega) \Delta R$
Resistance to solder heat	MIL-STD-202, method 210, + 260 °C solder, 10 s to 12 s dwell, 25 mm/s emergence	$\pm (1.0 \% + 0.0005 \Omega) \Delta R$
Moisture resistance	MIL-STD-202, method 106, 0 % power, 7a and 7b not required	$\pm (2.0 \% + 0.0005 \Omega) \Delta R$

PACKAGING					
MODEL	REEL				
	TAPE WIDTH	DIAMETER	PITCH	PIECES/REEL	CODE
RCWE0402	8 mm/punched paper	180 mm/7"	2 mm	10 000	EA
RCWE0603	8 mm/punched paper	180 mm/7"	4 mm	5000	EA
RCWE0805	8 mm/punched paper	180 mm/7"	4 mm	5000	EA
RCWE1206	8 mm/punched paper	180 mm/7"	4 mm	5000	EA
RCWE1210	8 mm/punched paper	180 mm/7"	4 mm	5000	EA
RCWE2010	12 mm/embossed plastic	180 mm/7"	4 mm	4000	EA
RCWE2512	12 mm/embossed plastic	180 mm/7"	8 mm	2000	EA

Note

- Embossed carrier tape per EIA-481-1A.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.