

# RR series, high-precision metal film chip resistors




Thin Film Technology has achieved high performance chip resistors with low price and reliable supply. The parts offer excellent performance and tolerance in TCR, current noise, linearity, for high frequency circuit applications. Precise dimensions minimize errors during mounting. Tight tolerance allow for cost saving due to circuit simplification and elimination of trim pots for adjustment.

RoHS compliant Completely lead free



## SPECIFICATIONS

### Mechanical



Dimension (Inch Size)	RR0306 (0201)	RR0510 (0402)	RR0816 (0603)	RR1220 RN73 (0805)	RR1632 (1206)	RR2632 (1210)
L	0.60±0.05	1.00±0.05	1.60±0.20	2.00±0.20	3.20±0.20	3.20±0.20
W	0.30±0.05	0.50±0.05	0.80±0.20	1.25±0.20	1.60±0.20	2.60±0.20
P	0.12±0.05	0.20±0.10	0.30±0.20	0.40±0.20	0.50±0.20	0.50±0.20
T	0.23±0.03	0.35±0.05	0.40±0.10	0.40±0.10	0.40±0.10	0.40±0.10

(unit : mm)

### Electrical

Type	RR0306	RR0510	RR0816	RR1220	RN73	RR1632	RR2632
Power	1/20W	1/16W	1/16W	1/10W	1/10W	1/8W	1/4W
Tolerance %(code)	±1.0% (F) ±0.5% (D)	±0.5% (D)	±0.5% (D)	±0.5% (D)	±0.1% (B)	±0.5% (D) ±0.1% (B)	±0.5% (D) ±0.1% (B)
Resistance Range (Ω)	10~30 33~22k	10~97.6 100~100k	10~97.6 100~360k	10~97.6 100~1M	511~100k 100~100k	10~49.9 51~1M 100~200k 100~200k 51~1M	10~49.9 51~2M 100~330k 100~330k 51~2M
TCR ppm /°C(code)	±100 (R) ±25 (P)	±100 (R) ±25 (P)	±50 (Q) ±25 (P)	±50 (Q) ±25 (P)	±5 (V) ±10 (N)	±50 (Q) ±25 (P) ±5 (V) ±10 (N) ±25 (P)	±50 (Q) ±25 (P) ±5 (V) ±10 (N) ±25 (P)
Resistance Value	E-24	E-24/E-96	E-24/E-96	E-24/E-96	E-24/E-96	E-24/E-96	E-24/E-96
Max Operating Voltage	15V	25V	75V	100V	100V	150V	150V
Package	5,000 pcs/reel	10,000 pcs/reel	5,000 pcs/reel	5,000 pcs/reel	1,000(T1)· 5,000(T5)pcs/reel	1,000(T1)· 5,000(T5)reel	1,000(T1)· 5,000(T5)reel

· Contact us also for RL0816-JMP jumper resistor whose dimensions are the same as those of RR0816.



## PART NUMBER

