















■ OVERTRAVEL TYPE SIDE ROTARY SWITCHES

Total travel 80 degrees, without one-way operation option, 1/2-14NPT conduit (-TS type)

Actuator 		Part number					
		Complete switch 	Head with lever 	Lever 	Head 	Built-in switch 	Leverless 
Roller lever	Short (38 mm radius), standard sensitivity	<b>WLH2-TS</b>	<b>WL-2H1100</b>	<b>WL-1A100</b>	<b>WL-2H</b>	<b>W-10FB3</b>	<b>WLRH2-TS</b>
	Short, high sensitivity	<b>WLG2-TS</b>				<b>W-10FB3-8</b>	<b>WLRG2-TS</b>
Adj. roller lever	Standard sensitivity	<b>WLH12-TS</b>	<b>WL-2H2100</b>	<b>WL-2A100</b>		<b>W-10FB3</b>	<b>WLRH2-TS</b>
	High sensitivity	<b>WLG12-TS</b>				<b>W-10FB3-8</b>	<b>WLRG2-TS</b>
Adj. rod lever	140 mm, std. sensitivity	<b>WLHL-TS</b>	<b>WL-2H4100</b>	<b>WL-4A100</b>		<b>W-10FB3</b>	<b>WLRH2-TS</b>
	140 mm, high sensitivity	<b>WLGL-TS</b>				<b>W-10FB3-8</b>	<b>WLRG2-TS</b>
	380 mm, std. sensitivity	<b>WLHAL4-TS</b>			<b>WL-2H3100</b>	<b>WL-3A100</b>	<b>W-10FB3</b>
Spring rod lever		<b>WLHAL5-TS</b>	<b>WL-2H3200</b>	<b>WL-3A200</b>		<b>W-10FB3</b>	<b>WLRH2-TS</b>








■ OVERTRAVEL TYPE SIDE ROTARY SWITCHES

Total travel 90 degrees, with one-way operation option (-2N type), 1/2-14NPT conduit (-TS type)

Actuator 		Part number					
		Complete switch 	Head with lever 	Lever 	Head 	Built-in switch 	Leverless 
Roller lever	Short (38 mm radius)	<b>WLCA2-2NTS</b>	<b>WL-6H1100</b>	<b>WL-1A100</b>	<b>WL-6H</b>	<b>W-10FB3</b>	<b>WLRCA2-2NTS</b>
Adj. roller lever		<b>WLCA12-2NTS</b>	<b>WL-6H2100</b>	<b>WL-2A100</b>			<b>WLRCA12-2NTS</b>
Adj. rod lever, 140 mm		<b>WLCL-2NTS</b>	<b>WL-6H3100</b>	<b>WL-3A100</b>			<b>WLRCA4-2NTS</b>




■ HIGH PRECISION TYPE SIDE ROTARY SWITCHES

Total travel 45 degrees, with one-way operation option, 1/2-14NPT conduit (-TS type)

Actuator 		Part number					
		Complete switch 	Head with lever 	Lever 	Head 	Built-in switch 	Leverless 
Roller lever	Short (38 mm radius)	<b>WLGCA2-TS</b>	<b>WL-1H1100-1</b>	<b>WL-1A100</b>	N/A	<b>W-10FB3-4</b>	<b>WLRGCA2-TS</b>
	Medium (50 mm radius)	<b>WLGCA2-7TS</b>	<b>WL-1H1200-1</b>	<b>WL-1A200</b>			
	Long (63 mm radius)	<b>WLGCA2-8TS</b>	<b>WL-1H1300-1</b>	<b>WL-1A300</b>			
Adjustable roller lever		<b>WLGCA12-TS</b>	<b>WL-1H2100-1</b>	<b>WL-2A100</b>			
Adjustable rod lever (140 mm)		<b>WLGCL-TS</b>	<b>WL-4H4100-1</b>	<b>WL-4A100</b>			<b>WLRGCL-TS</b>




## ■ PLUNGER SWITCHES

### 1/2-14NPT conduit (-TS type)

Actuator	Part number		
	Complete switch	Head with actuator	Built-in switch
			
Top plunger	<b>WLD-TS</b>	<b>WL-7H100</b>	<b>W-10FB3</b>
Top roller plunger	<b>WLD2-TS</b>	<b>WL-7H200</b>	
Top sealed roller plunger	<b>WLD28-TS</b>	<b>WL-7H400</b>	
Top ball plunger	<b>WLD3-TS</b>	<b>WL-7H300</b>	
Horizontal plunger	<b>WLS-D-TS</b>	<b>WL-8H100</b>	<b>W-10FB3-4</b>
Horizontal roller plunger	<b>WLS-D2-TS</b>	<b>WL-8H200</b>	
Horizontal ball plunger	<b>WLS-D3-TS</b>	<b>WL-8H300</b>	

## ■ COIL SPRING / STEEL WIRE SWITCHES

### 1/2-14NPT conduit (-TS type)

Actuator	Part number		
	Complete switch	Head with actuator	Built-in switch
			
Coil spring, 6.5 mm dia.	<b>WNJ-TS</b>	<b>WL-9H100</b>	<b>W-10FB3</b>
Coil spring, 5.0 mm dia.	<b>WLNJ30-TS</b>	<b>WL-9H200</b>	
Steel wire, 1.0 mm dia.	<b>WLNJ-S2TS</b>	<b>WL-9H400</b>	
Nylon rod, 8.0 mm dia.	<b>WLNJ-2TS</b>	<b>WL-9H300</b>	

## ■ STATUS INDICATOR EQUIPPED SWITCHES

Any of the WL switches above can be ordered with a neon or LED indicator that shows normally open and normally closed status. For a neon indicator, add "-LE" to the end of a part number, for example, **WLD2-TSLE**. For an LED indicator, add "-LD" to the end of a part number, for example, **WLCA2-TSLD**.